

# YS29LB

by Burndy  
Catalog ID: YS29LB

Prop 65 Notice

Copper Compression Splice, 4/0 Flex, 2.40" Splice Length, Short Barrel, Belled End, Tin Plated



## Product Details

### General

Color Code	Yellow
Connector Type	Splice
Die Index	16
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810508022
UPC 12 Digit	7818105080222

### Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.04 in
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.40 in
Dimension - Strip Length inch	1-1/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Str Compact Size	250 kcmil
Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Size	250 kcmil

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)