

YS29L

by Burndy
Catalog ID: YS29L

Prop 65 Notice

Hylink Cu compression standard barrel code splice tubing, Beveled entry, 250 kcmil .Cu, 600V-35KV, Tin plated



Product Details

General

Color Code	Yellow
Connector Type	Splice
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810070284
UPC 12 Digit	7818100702844

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.46 in
Dimension - Strip Length inch	1-1/8

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Compact Size	250
Conductor - Copper Str Size	250 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)