

YS29PULL

by Burndy
Catalog ID: YS29PULL

Hylink Cu compression long barrel code splice tubing, Beveled entry, 250 kcmil.CU, 600V-35KV, Tin plated, Yellow, 16 Index.

Features: Long barrel length, Four center conductor stops, High pull out force



Product Details

General

Application	For heavy duty applications
Color Code	Yellow
Connector Type	Splice
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	YS
UPC	781810090176
UPC 12 Digit	7818100901766

Dimensions

Dimension - B Length inch	1.58 in
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.58 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	250 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)