



## YS2CFXLTCKITC

by Burndy  
Catalog ID: YS2CFXLTCKITC

Prop 65 Notice

Electro-tin plated copper compression reducer/splice, with a through hole for cable inspection on each side, for 2 AWG wire.

### Product Details

#### General

|                        |                      |
|------------------------|----------------------|
| Color Code             | Brown                |
| Color Code - Side A    | Brown                |
| Color Code - Side B    | Brown                |
| Connector Type         | Splice;Reducer       |
| Die Index              | 10                   |
| Die Index Run Side     | 10                   |
| Die Index Tap Side     | 10                   |
| Feature - Barrel Style | Skived               |
| Feature - Barrel Type  | Standard             |
| Material               | Copper               |
| Plated                 | Y                    |
| Plating Type           | Tin - Electro Plated |
| Temperature Rating     | 194                  |
| Trade Name             | HYSPLICE™            |
| UPC                    | 781810344163         |
| UPC 12 Digit           | 7818103441633        |

#### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 0.78 in |
| Dimension - L Length Overall mm | 47.7 mm |
| Dimension - Length BB inch      | 0.78 in |
| Dimension - Length Overall inch | 1.88 in |
| Dimension - Strip Length inch   | 0.78 in |

#### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

#### Conductor Related

|                                  |       |
|----------------------------------|-------|
| Conductor - Copper Flex G Size A | 2 AWG |
| Conductor - Copper Flex G Size B | 2 AWG |

|                                  |       |
|----------------------------------|-------|
| Conductor - Copper Flex H Size A | 2 AWG |
| Conductor - Copper Flex H Size B | 2 AWG |
| Conductor - Copper Flex I Size A | 2 AWG |
| Conductor - Copper Flex I Size B | 2 AWG |
| Conductor - Copper Flex K Size A | 2 AWG |
| Conductor - Copper Flex K Size B | 2 AWG |
| Conductor - Copper Flex M Size A | 2 AWG |
| Conductor - Copper Flex M Size B | 2 AWG |
| Conductor - Copper Str Size      | 2 AWG |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)