

YS2CL

by Burndy
Catalog ID: YS2CL

Prop 65 Notice

In-line splice, # 60(.282)(navy),2 STR(.291)(COM'L Cable), Tin plated, Brown, 10 index.

Standard barrel length, Four center conductor stops



Product Details

General

Application	For limited space applications while providing ample barrel length for proper crimp
Color Code	Brown
Connector Type	Splice
Die Index	10;97
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	YSL
UPC	781810111628
UPC 12 Digit	7818101116288

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Strip Length inch	15/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Compact Size	2
Conductor - Copper Str Size	2 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)