

## YS31FXB

by Burndy  
Catalog ID: YS31FXB

Cu compression splice, 263 kcmil, 600V-35KV, Long barrel, belled end, Tin plated



### Product Details

#### General

Color Code	White
Connector Type	Splice
Die Index	17
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810041512
UPC 12 Digit	7818100415122

#### Dimensions

Dimension - B Length inch	2.18 in
Dimension - D inch	1.03 in
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.54 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Strip Length inch	2-1/4

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper DLO Size	262.6 (650/#24) DLO
Conductor - Copper Flex I Size	250 kcmil
Conductor - Copper Flex K Size	250 kcmil
Conductor - Copper Flex M Size	250 kcmil
Conductor - Copper Str Size	250

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)