

## YS32L

by Burndy  
Catalog ID: YS32L

Prop 65 Notice

Cu Comp Butt Splice(Code), 400 Navy, 400 kcmi(Com'l Cable), 600 V-35 kV, 2.74" L, Std bbl, Tin Plated, Blue.

Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W32CVT Die, (2), Y35, Y39, Y750, Y46 Tool, U32CRT Die, (2), Die Index: 19 Element A, Color Code: Blue, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Wire Strip Length: 1/4 IN



## Product Details

### General

Application	For Limited Space Applications
Color Code	Blue
Connector Type	Splice
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810508459
UPC 12 Digit	7818105084599

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.74 in
Dimension - Strip Length inch	1-1/4

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Compact Size	400
-------------------------------------	-----

Conductor - Copper Str Size	400 kcmil
-----------------------------	-----------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)