

YS36FXB

by Burndy
Catalog ID: YS36FXB

Prop 65 Notice

Hylink Cu compr long barrel code splice tubing, Beveled entry, 444.4 kcmil(1100/24) 450kcmil Nom, 444.4 kcmil(1100/24) 450kcmil Nom, Brown, 20 Index.

Features: Hylink Copper Compression long barrel code splice tubing, Brown, 20 Index



Product Details

General

Application	Splicing
Color Code	Brown
Connector Type	Splice
Die Index	20
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	SPLICE, HYLINK
Temperature Rating	194
Trade Name	HYLINK™
Type	Type YS-FXB
UPC	781810056899
UPC 12 Digit	7818100568999

Dimensions

Dimension - B Length inch	2.95 in
Dimension - D inch	1.40 in
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.09 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Strip Length inch	3-1/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 (1100/#24) DLO
-----------------------------	----------------------

Conductor - Copper Flex G Size	450 kcmil
Conductor - Copper Flex H Size	450 kcmil
Conductor - Copper Flex I Size	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Str Size	450 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)