

# YS36L

by Burndy  
Catalog ID: YS36L

Prop 65 Notice

Cu Comp Butt Splice(Code), 600 kcmil(Com'l Cable), 600 V-35 kV, 3.22" L, Std bbl, Tin Plated, Green.

Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750, Y46 Tool, U36CRT Die, (2), Die Index: 22 Element A, Color Code: Green, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Wire Strip Length: 1-7/16 IN



## Product Details

### General

Application	For Limited Space Applications
Color Code	Green
Connector Type	Splice
Die Index	22;472
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810526408
UPC 12 Digit	7818105264088

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.22 in
Dimension - Strip Length inch	1-7/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Compact Size	600
-------------------------------------	-----

Conductor - Copper Str Size	600 kcmil
-----------------------------	-----------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)