

## YS36PULL

by Burndy  
Catalog ID: YS36PULL

Cu compression splice, 600 kcmil, Green, 22 or 472index.

Long barrel length, Four center conductor stops, High pull out force



## Product Details

### General

Application	For heavy duty applications
Color Code	Green
Connector Type	Splice
Die Index	22;472
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	YS
UPC	781810093436
UPC 12 Digit	7818100934366

### Dimensions

Dimension - B Length inch	2.63 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.86 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	600 kcmil
-----------------------------	-----------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)