

## YS37

by Burndy  
Catalog ID: YS37

Copper Compression Splice, 650 Kcmil, 6.10" Splice Length, Long Barrel, Tin Plated



## Product Details

### General

Color Code	Orange
Connector Type	Splice
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810080863
UPC 12 Digit	7818100808633

### Dimensions

Dimension - B Length inch	2.75 in
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.10 in
Dimension - Strip Length inch	2-13/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	650 (127)
Conductor - Copper Str Size	650

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	6
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)