



## YS38FXLTCKITC

by Burndy  
Catalog ID: YS38FXLTCKITC

Prop 65 Notice

Electro-tin plated copper compression reducer/splice, with a through hole for cable inspection on each side, for 500 Kcmil wire.

### Product Details

#### General

Color Code	Pink
Color Code - Side A	Pink
Color Code - Side B	Pink
Connector Type	Splice;Reducer
Die Index	L99
Die Index Run Side	L99
Die Index Tap Side	L99
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSPLICE™
UPC	781810343999
UPC 12 Digit	7818103439999

#### Dimensions

Dimension - B Length inch	1.77 in
Dimension - L Length Overall mm	109.22 mm
Dimension - Length BB inch	1.77 in
Dimension - Length Overall inch	4.3 in
Dimension - Strip Length inch	1.77

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper Flex G Size A	500 kcmil
Conductor - Copper Flex G Size B	500 kcmil

Conductor - Copper Flex H Size A	500 kcmil
Conductor - Copper Flex H Size B	500 kcmil
Conductor - Copper Flex I Size A	500 kcmil
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex K Size A	500 kcmil
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex M Size A	500 kcmil
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Str Size	500 Kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)