

YS39LFXG1

by Burndy
Catalog ID: YS39LFXG1

Copper compression splice standard barrel, bare, 573.1 Kcmil wire size, 2.32 in length



Product Details

General

Connector Type	Splice
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810083666
UPC 12 Digit	7818100836666

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Inside Diameter inch	1.03 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Strip Length inch	1-11/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	571
Conductor - Copper Flex H Size	571
Conductor - Copper Flex I Size	571
Conductor - Copper Flex K Size	571
Conductor - Copper Flex M Size	571

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	15
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)