

# YS44FXB

by Burndy  
Catalog ID: YS44FXB

Prop 65 Notice

Copper Compression Splice, 777.7 kcmil, 6.84" Splice Length, Long Barrel, Tin Plated



## Product Details

### General

Color Code	Yellow
Connector Type	Splice
Die Index	L115
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810080887
UPC 12 Digit	7818100808877

### Dimensions

Dimension - B Length inch	3.33 in
Dimension - D inch	1.76 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.84 in
Dimension - Outside Diameter inch	1.49 in
Dimension - Strip Length inch	3-7/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24) DLO
Conductor - Copper Str Size	750 kcmil

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)