



YS44FXLTCKITC

by Burndy
Catalog ID: YS44FXLTCKITC

Prop 65 Notice

Electro-tin plated copper compression reducer/splice, with a through hole for cable inspection on each side, for 750 Kcmil wire.

Product Details

General

Color Code	Yellow
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Connector Type	Splice;Reducer
Die Index	L115
Die Index Run Side	L115
Die Index Tap Side	L115
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSPLICE™
UPC	781810343951
UPC 12 Digit	7818103439511

Dimensions

Dimension - B Length inch	1.96 in
Dimension - L Length Overall mm	122.17 mm
Dimension - Length BB inch	1.96 in
Dimension - Length Overall inch	4.81 in
Dimension - Strip Length inch	1.96

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size A	750
Conductor - Copper Flex G Size B	750

Conductor - Copper Flex H Size A	750
Conductor - Copper Flex H Size B	750
Conductor - Copper Flex I Size A	750
Conductor - Copper Flex I Size B	750
Conductor - Copper Flex K Size A	750
Conductor - Copper Flex K Size B	750
Conductor - Copper Flex M Size A	750
Conductor - Copper Flex M Size B	750
Conductor - Copper Str Size	750 Kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)