



YS48A1

by Burndy
Catalog ID: YS48A1

Prop 65 Notice

Aluminum Compression Splice, 2000 kcmil, 7.58" Splice Length, Long Barrel, Tin Plated.

Product Details

General

Color Code	Red
Connector Type	Splice
Die Index	479
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810166727
UPC 12 Digit	7818101667277

Dimensions

Dimension - B Length fraction	3-11/16 in
Dimension - B Length inch	3.66 in
Dimension - L Length Overall mm	193 mm
Dimension - Length Overall inch	7.58 in
Dimension - Outside Diameter inch	2.60 in
Dimension - Strip Length inch	4-1/8 in
Length	7.58 in
Outside Diameter	2.6 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	2000 kcmil
Conductor - AL Str Size Range	2000 kcmil

Conductor - Copper Str Size	2000 kcmil
Conductor - Copper Str Size Range	2000 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)