

YS8CFXB

by Burndy
Catalog ID: YS8CFXB

Prop 65 Notice

Copper Compression Splice, 8 Flex, 1.99" Splice Length, Long Barrel, Belled End, Tin Plated



Product Details

General

Color Code	Red
Connector Type	Splice
Die Index	49
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810082904
UPC 12 Digit	7818100829044

Dimensions

Dimension - B Length inch	0.90 in
Dimension - D inch	0.32 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	1.99 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Strip Length inch	1 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	8 (37/#24) DLO
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex K Size	8 AWG

Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Navy Size	23 (7)
Conductor - Copper Str Size	8 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)