

# YSA33R2N

by Burndy  
Catalog ID: YSA33R2N

Prop 65 Notice

HYLUG™, DISCONNECTABLE TERMINAL, Barrel Partially filled with Penetrox™ and Sealed tongues coated with an oxide retardant, Accommodates: 397.5 KCMIL- 477 KCMIL ASCR; 397 KCMIL - 400 KCMIL Aluminum conductors.



## Product Details

### General

Connector Type	Terminal
Die Index	317
Material	Aluminum
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	3
Physical Attribute - Number of Holes	2
Prefilled Oxide Inhibitor	Y
UPC	781810262122

### Dimensions

Dimension - B Length fraction	3-3/50 in
Dimension - B Length inch	3.06 in
Dimension - D inch	3.25 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	196 mm
Dimension - Length Overall inch	7.71 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.9 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - ACSR Str Size	336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee
Conductor - AL Str Size	397.5 KCMIL- 400 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)