



YSCM167

by Burndy
Catalog ID: YSCM167

Prop 65 Notice

Colour coded uninsulated YSCM seamless parallel splice connectors, Beveled entry, 134340(Min), 166560(Max), Up to 600V, Tin plated, Orange, 14 Index.

Features: Type YSCM HYLINK Seamless Parallel Splice Connectors Permit Stranded Wires To Be Laid Parallel Inside The Connector And Spliced Together With BURNDY Compression Tools, Each YSCM Connector Accommodates A Wide Range Of Conductors And Is Color-Coded To Ensure Proper Tool And Die Match, YSCM Connectors Are UL486A Listed For Applications Up To 600V And CSA Listed, Die Index: 14, Wire Strip Length: 1-1/16 IN, Color Code: Orange, Tools, Die Set Catalog Number, And (number Of Crimps): OUR840, Y500THS, PAT60018V Tool, X27RT, W27RT Die, Y35, Y750, PAT750 Tool, U27RT Die

Product Details

General

Application	Type YSCM HYLINK seamless parallel splice connectors permit stranded wires to be laid parallel inside the connector and spliced together with BURNDY compression tools
Color Code	Orange
Connector Type	Splice
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSCM
UPC	781810358566
UPC 12 Digit	7818103585666

Dimensions

Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)