

YSD27R2R

by Burndy
Catalog ID: YSD27R2R

Prop 65 Notice

AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Black (Side A), Red (Side B)



Product Details

General

| | |
|---------------------------|-------------------------------|
| Color Code - Side A | Black |
| Color Code - Side B | Red |
| Die Index | 249;K-840 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | LINKIT™ |
| Type | Service Entrance, Uninsulated |
| UPC | 781810145005 |
| UPC 12 Digit | 7818101450055 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 102 mm |
| Dimension - Length Overall inch | 4 in |
| Dimension - Outside Diameter inch | .3125 in |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - ACSR Str Size A | 3/0 (6/1) Pigeon AWG |
| Conductor - ACSR Str Size B | 2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG |
| Conductor - ACSR Str Size B Range | 2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG |
| Conductor - AL Str Size A | 3/0 AWG |
| Conductor - AL Str Size B | 1 AWG, 2 AWG |
| Conductor - AL Str Size B Range | 1 AWG-2 AWG |
| Conductor - Copper Str Size A | 3/0 AWG |
| Conductor - Copper Str Size B | 1 AWG, 2 AWG |
| Conductor - Copper Str Size B Range | 1 AWG-2 AWG |

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |

| | |
|------------------------------------|----|
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)