

# YSD28R25RBOX100

by Burndy  
Catalog ID: YSD28R25RBOX100

Prop 65 Notice

Al LINKIT Splice Box, 4/0 AWG ACSR/Al/Cu, 300 kcmil Al Comp.(Side A),  
1/0 AWG ACSR/Al/Cu, 2/0 AWG Al Comp.(Side B)



## Product Details

### General

Color Code - Side A	Pink
Color Code - Side B	Yellow
Die Index	249;840
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	LINKIT™
Type	Service Entrance, Uninsulated
UPC	781810047064
UPC 12 Digit	7818100470644

### Dimensions

Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Outside Diameter inch	.3125 in

### Conductor Related

Conductor - ACSR Str Size A	4/0 AWG
Conductor - ACSR Str Size B	1/0 Awg
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	1/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)