

YSE10BOX

by Burndy
Catalog ID: YSE10BOX

Prop 65 Notice

Cu Butt Splice, Smooth Funnel Entry, W/InspWindow, AN12-10, 600 V, 1.15" L, Nylon Insul, Integral bbl, Tin Plated, Yellow.

Features: The Types YSE And YSE-H INSULINKS Are High Quality Nylon Insulated Butt Splices Designed For Splicing Aircraft And Commercial Flexible Cables, Manufactured From Tin Plated, Seamless Electrolytic Copper Tubing With Integral Barrel/Insulation Grip: Provides Maximum Conductivity And Tensile Strength, Plus Excellent Cable Support And Strain Relief, Split Heavy Wall Insulation Grip: Provides Stronger Insulation Grip And Strain Relief, Smooth Funnel Entry: Provides Easy Wire Insertion, Transparent Nylon Insulation: Permits Easy Wire Inspection, Package: Box, Insulation Support: No, Installation Tool: Y10D Tool, Ratchet: MR8-33S-1 Tool, Color Code: Yellow, Wire Strip Length: 23/64 IN, Conductor Type: Commercial/Aircraft Stranded Copper



Product Details

General

Application	For Splicing Aircraft And Commercial Flexible Cables
Color Code	Yellow
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	INSULINK
Temperature Rating	105
Trade Name	INSULINK™
Type	YSE
UPC	781810566305
UPC 12 Digit	7818105663055

Dimensions

Cable Insulation Diameter Maximum	0.209 in
Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - Diameter Max Size inch	0.22 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.15 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	23/64 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)