

YSE10HHS

by Burndy
Catalog ID: YSE10HHS

Elect Cu Heat Shrink Butt Splice, Smooth Funnel Entry, 10-12 AWG, 600 V, 1.60" L, Integral bbl, Tin Plated, Yellow(Insul Color).

Features:Elect Cu Heat Shrink Butt Splice, Smooth Funnel Entry, 10-12 AWG, 600 V, 1.60 IN L, Integral barrel, Tin Plated, Yellow(Insul Color)



Product Details

General

Application	Butt Connector
Connector Type	Heat Shrink Butt Splice
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYDENT
Trade Name	HYDENT™
Type	YSE-HHS
UPC	781810525470

Dimensions

Dimension - Inside Diameter inch	0.25 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.60 in
Dimension - Strip Length inch	23/64 in

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
-----------------	--------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)