

YSE10

by Burndy
Catalog ID: YSE10

600 VOLTS, 105° C.



Product Details

General

Color Code	Yellow
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	105
Trade Name	INSULINK™
UPC	781810803844
UPC 12 Digit	7818108038444

Dimensions

Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - Diameter Max Size inch	0.22 in
Dimension - Length Overall inch	1.15 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	23/64

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)