

# YSE18HHS

by Burndy  
Catalog ID: YSE18HHS



Elect Cu Heat Shrink Butt Splice, Smooth Funnel Entry, 18-22 AWG, 600 V, 1.50" L, Integral bbl, Tin Plated, Red(Insul Color).

Features: The Types YSE And YSE-H INSULINKS Are High Quality Nylon Insulated Butt Splices Designed For Splicing Aircraft And Commercial Flexible Cables, Manufactured From Tin Plated, Seamless Electrolytic Copper Tubing With Integral Barrel/Insulation Grip: Provides Maximum Conductivity And Tensile Strength, Plus Excellent Cable Support And Strain Relief, Split Heavy Wall Insulation Grip: Provides Stronger Insulation Grip And Strain Relief, Smooth Funnel Entry: Provides Easy Wire Insertion, Transparent Nylon Insulation: Permits Easy Wire Inspection, Installation Tool: Y10D Tool, Ratchet: MR8-33S-1 Tool, Color Code: Red, Wire Strip Length: 9/32 IN, Conductor Type: Commercial/Aircraft Stranded Copper

## Product Details

### General

Application	For Splicing Aircraft And Commercial Flexible Cables
Connector Type	Heat Shrink Butt Splice
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YSE-H, Heat Shrink
UPC	781810525494

### Dimensions

Dimension - Inside Diameter inch	0.17 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Strip Length inch	9/32 in

### Conductor Related

Conductor Range	#18 AWG to #22 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)