



YSE18H

by Burndy
Catalog ID: YSE18H

Prop 65 Notice

600 VOLTS, 105° C.

Product Details

General

Color Code	Red
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	105
Trade Name	INSULINK™
UPC	781810803882
UPC 12 Digit	7818108038822

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - Length Overall inch	1.20 in
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	9/32

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Size	20;18
Conductor - Copper Str Size Range	20-18
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)