



YSES10K

by Burndy
Catalog ID: YSES10K

Prop 65 Notice

RADIATION RESISTANT INSULATED BUTT SPLICE, POLYVINYLIDENE FLOURIDE (PVF2) INSULATED.

Product Details

General

Color Code	Yellow
Connector Type	Splice
Insulation	Y
Insulation Type	Kynar
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	150
Trade Name	INSULINK™
Type	Radiation Resistant KYNAR Splice
UPC	781810126820
UPC 12 Digit	7818101268200

Dimensions

Cable Insulation Diameter Maximum	0.210 in
Dimension - B Length fraction	9/25 in
Dimension - B Length inch	0.36 in
Dimension - Diameter Max Size inch	0.21 in
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.30 in
Dimension - P inch	0.04 in
Dimension - Pad Width inch	0.21 in
Dimension - Strip Length inch	7/16 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12;10
Conductor - Copper Str Size Range	12-10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	500

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)