

YSES142

by Burndy
Catalog ID: YSES142

BUTT SPLICE, NYLON INSULATED MS25181, CLASS 1 SPLICE, 300 VOLTS, 105° C.



Product Details

General

Color Code	Blue
Connector Type	Splice
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	105
Trade Name	INSULINK™
UPC	781810804582
UPC 12 Digit	7818108045822

Dimensions

Dimension - B Length fraction	1-44/83 in
Dimension - B Length inch	1.53 in
Dimension - D inch	0.23 in
Dimension - Length Overall inch	1.53 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Pad Width inch	0.15 in
Dimension - Strip Length inch	7/32 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)