



YSH3931

by Burndy
Catalog ID: YSH3931

Prop 65 Notice

Copper Splice, 750 - 350 Kcm (Run), 4/0 - 1/0 AWG (350-1/0) (Tap 1), #1-#6 AWG (1-8) (Tap 2), #2-#14 AWG (2-14) (Tap 3), KR Index

Product Details

General

| | |
|----------------|---------------|
| Color Code | Yellow |
| Connector Type | H-Tap |
| Die Index | KR |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Type | Taps |
| UPC | 781810038413 |
| UPC 12 Digit | 7818100384133 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 2.97 in |
| Dimension - Length Overall inch | 3.00 in |
| Dimension - Strip Length inch | 1 1/2 |
| Dimension - Width inch | 1.50 in |
| Dimension - Width mm | 38 mm |

Conductor Related

| | |
|-------------------------------------|---|
| Conductor - Copper Flex G Run | 350 kcmil;400 kcmil;450 kcmil;500 kcmil;600 kcmil;700 kcmil |
| Conductor - Copper Flex G Run Range | 350 kcmil-700 kcmil |
| Conductor - Copper Flex G Tap | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil |
| Conductor - Copper Flex G Tap Range | 1/0 AWG-350 kcmil |
| Conductor - Copper Flex H Run | 350 kcmil;400 kcmil;450 kcmil;500 kcmil;600 kcmil;700 kcmil |
| Conductor - Copper Flex H Run Range | 350 kcmil-700 kcmil |
| Conductor - Copper Flex H Tap | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil |
| Conductor - Copper Flex H Tap Range | 1/0 AWG-350 kcmil |
| Conductor - Copper Str Run | 350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil |
| Conductor - Copper Str Run Range | 350 kcmil-750 kcmil |
| Conductor - Copper Str Tap | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil |
| Conductor - Copper Str Tap Range | 1/0 -350 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 20 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)