



## YSHG3429

by Burndy  
Catalog ID: YSHG3429

Prop 65 Notice

Copper Compression Double H- Tap Connector, 3/0 - 1/0 AWG (Tap 1)/ 1 - 4 AWG ( Tap 2)/ 8 -14 AWG (Tap 3), # 6 Rebar/ 3/4" Ground Rod/ 400 to 4/0 kcmil Cu Cable.

Features: UL467 Listed: Suitable For Direct Burial In Earth Or Concrete, Material Is High Conductivity Copper Extrusion: Minimizes Resistance, Eliminates Corrosion Due To Dissimilar Metals, Grooves Are Prefilled With PENETROX E2 Oxide Inhibitor And Individually Sealed: Inhibits Moisture And Contaminants Ensuring Electrical Integrity, Tools, Die Set Catalog Number, And (number Of Crimps): Y750, PAT750 Tool, U1104 Die, (4), Y46 Tool, P1104 Die, (2), U1104 Die With PUADP-1 Adapter, (4), Rebar Size: #6, Wire Entry: Double, Conductor Type: Run: Rebar, Tap1: Copper Wire, Tap2: Copper Wire, Tap3: Copper Wire, Die Index: 1104 Element A, Shape: H, Conductor Size (tap Range): Tap1: 1/0 - 3/0 AWG, Tap2: 4 - 1 AWG, Tap3: 8 AWG

## Product Details

### General

Application	For Direct Burial In Earth Or Concrete
Connector Type	H-Tap
Die Index	1104
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	HYGROUND®
Type	Taps
UPC	781810129715
UPC 12 Digit	7818101297155

### Dimensions

Dimension - Length Overall inch	2.44 in
Dimension - Width inch	2.23 in
Dimension - Width mm	57 mm

### Conductor Related

Conductor - Copper Str Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Run Range	4/0 AWG-400 kcmil
Conductor - Copper Str Tap	3/0 - 1/0 AWG (Tap 1)/ 1 - 4 AWG ( Tap 2)/ 8 -14 AWG (Tap 3)
Conductor - Copper Str Tap Range	3/0 - 1/0 AWG (Tap 1)/ 1 - 4 AWG ( Tap 2)/ 8 -14 AWG (Tap 3)
Conductor - Rebar Run	6
Conductor - Rebar Run Range	6
Conductor - Rod Run	3/4 in

Conductor - Rod Run Range	3/4 in
---------------------------	--------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)