



YSHG3939

by Burndy
Catalog ID: YSHG3939

Prop 65 Notice

Copper Compression Double H- Tap Connector, 1" Ground Rod or 500 kcmil (Run), 500 -350 kcmil (Tap)

Product Details

General

Connector Type	H-Tap
Die Index	KR
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
Type	Taps
UPC	781810129562
UPC 12 Digit	7818101295622

Conductor Related

Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap Range	500-350 kcmil
Conductor - Rod Run Range	1" Ground rod

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)