



YSM10

by Burndy
Catalog ID: YSM10

Copper Compression Parallel Splice, 4107-10380 Circular Mil, 0.36" Splice Length, Short Barrel, Tin Plated.

Features: HYLINK Type YSM Seamless Parallel Splice Connector Permits Wires To Be Laid Parallel Inside The Connector And Spliced Together With BURNDYs Compression HYTOOL, Each YSM Connector Accommodates A Wide Combination Of Round, Square, And Rectangular Copper Conductors That Have A Total Combined Circular Mil Area, The Conductors To Be Spliced Must Physically Fit Within Title Splice Without Being Forced, Installation Tool: Ratchet: MR8-9Q, MR4CQ Tool, Wire Strip Length: 7/16 IN

Product Details

General

| | |
|------------------------|--|
| Application | HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling |
| Connector Type | Splice |
| Feature - Barrel Style | Chamfered |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | HYLINK |
| Temperature Rating | 90 |
| Trade Name | HYLINK™ |
| Type | YSM |
| UPC | 781810805800 |
| UPC 12 Digit | 7818108058000 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - Length Overall inch | 0.36 in |
| Dimension - Outside Diameter inch | 0.21 in |
| Dimension - Strip Length inch | 7/16 |

Conductor Related

| | |
|-------------------------------------|--|
| Conductor - Copper Solid Size | 14 AWG;13 AWG;12 AWG;11 AWG;10 AWG |
| Conductor - Copper Solid Size Range | 14 AWG-10 AWG |
| Conductor - Copper Str Size | 14 AWG;12 AWG;10 AWG |
| Conductor - Copper Str Size Range | 14 AWG-10 AWG |
| Conductor Type | <ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |

| | |
|------------------------------------|----|
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 500 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)