



YSM27

by Burndy
Catalog ID: YSM27

Prop 65 Notice

Cu Uninsul Parallel Splice, BvI Entry, 133650-167332 cmil Cable,197000-250000 cmil Sol Wire, 0.81" L, Tin Plated.

Features: HYLINK Type YSM Seamless Parallel Splice Connector Permits Wires To Be Laid Parallel Inside The Connector And Spliced Together With BURNDYs Compression HYTOOL, Each YSM Connector Accommodates A Wide Combination Of Round, Square, And Rectangular Copper Conductors That Have A Total Combined Circular Mil Area, The Conductors To Be Spliced Must Physically Fit Within Title Splice Without Being Forced, Wire Strip Length: 7/8 IN, Installation Tool: Mechanical HYTOOL: MY29-11 Or MY28 Tool, (1), Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: Y35BH, Y39BH Tool, UV27L Die Nest, Y29PQ-6 Die Indentor, Y35P Indentor Adapter

Product Details

General

Application	HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810807156
UPC 12 Digit	7818108071566

Dimensions

Dimension - Length Overall inch	0.81 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Strip Length inch	7/8

Conductor Related

Conductor - Copper Str Size	2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	2/0 AWG-3/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)