



## YSM292

by Burndy  
Catalog ID: YSM292

Prop 65 Notice

Copper Parallel Splice, 275,000 - 211,500 cmils

### Product Details

#### General

|                        |               |
|------------------------|---------------|
| Connector Type         | Splice        |
| Feature - Barrel Style | Chamfered     |
| Material               | Copper        |
| Plated                 | Y             |
| Plating Type           | Tin           |
| Trade Name             | HYLINK™       |
| UPC                    | 781810083680  |
| UPC 12 Digit           | 7818100836800 |

#### Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - Length Overall inch   | 1.38 in |
| Dimension - Outside Diameter inch | 0.75 in |
| Dimension - Strip Length inch     | 1-7/16  |

#### Conductor Related

|                |   |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |
|----------------|---|

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

#### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)