

YSM31L78

by Burndy
Catalog ID: YSM31L78

Prop 65 Notice

Cu Tubing Parallel Splice, 350 kcmil, 0.82" L, Chamfered bbl, Tin Plated.

Features: Cu Tubing Parallel Splice, 350 kcmil, 0.82 IN L, Chamfered bbl, Tin Plated



Product Details

General

Application	Splicing
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Type	Splice
UPC	781810375716
UPC 12 Digit	7818103757166

Dimensions

Dimension - B Length inch	0.68 in
Dimension - Inside Diameter inch	0.68 in
Dimension - Length Overall inch	0.82 in
Dimension - Outside Diameter inch	0.88 in

Conductor Related

Conductor - Copper Str Compact Size	350 kcmil
Conductor - Copper Str Compact Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)