

YSM34L112

by Burndy
Catalog ID: YSM34L112

Prop 65 Notice

Cu Tubing Parallel Splice, 500 kcmil, 1.17" L, Chamfered bbl, Tin Plated.

Features: Cu Tubing Parallel Splice, 500 kcmil, 1.17 IN L, Chamfered bbl, Tin Plated



Product Details

General

Application	Splicing
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Type	Splice
UPC	781810371121
UPC 12 Digit	7818103711211

Dimensions

Dimension - B Length inch	0.82 in
Dimension - Inside Diameter inch	0.82 in
Dimension - Length Overall inch	1.17 in
Dimension - Outside Diameter inch	1.06 in

Conductor Related

Conductor - Copper Str Compact Size	500 kcmil
Conductor - Copper Str Compact Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)