

# YSM40L144

by Burndy  
Catalog ID: YSM40L144

Prop 65 Notice

Cu Tubing Parallel Splice, 800 kcmil, 1.48" L, Chamfered bbl, Tin Plated.

Features: Cu Tubing Parallel Splice, 800 kcmil, 1.48 IN L, Chamfered bbl, Tin Plated



## Product Details

### General

Application	Splicing
Connector Type	Splice
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	SPLICE CONNECTOR
Trade Name	HYLINK™
Type	Splice
UPC	781810371145
UPC 12 Digit	7818103711455

### Dimensions

Dimension - B Length inch	1.03 in
Dimension - Inside Diameter inch	1.03 in
Dimension - Length Overall inch	1.48 in
Dimension - Outside Diameter inch	1.35 in

### Conductor Related

Conductor - Copper Str Compact Size	800 kcmil
Conductor - Copper Str Compact Size Range	800 kcmil
Conductor - Copper Str Size	800 kcmil
Conductor - Copper Str Size Range	800 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

**Logistics**

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)