

YSP31T

by Burndy
Catalog ID: YSP31T

Prop 65 Notice

Uninsulated high voltage Cu -code compression splice, Tapered end, 350 kcmil, 600V-35KV, Tin plated, 18 Index.

Features: Seamless Types YSP-T High Conductivity Copper Electro-Tin Plated Compression HYLINK High-Voltage Splices With Long Barrel And Tapered Ends Are Ideally Suited For Higher Voltage Applications From 5KV Through 35 KV, Tapered Connector Ends Per EEI Standard TD160, Suitable For Use On Voltages 5KV Through 35KV To Aid In Preventing Corona Emission And Simplify Taping Thus Lowering Installed Cost, Type YSP-T Has A Center Plug Permanently Brazed In Place: Prevents Oil Within Oil-Filled Conductors From Passing Through The Splice Connector And Provides A Center Strip For Proper Conductor Insertion, Installation Tool: Y34B, Y34PR Indentor, B31D Nest Die, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: Y35, Y39, Y750 Tool, U31D-1 Nest Die, Y34PR Indentor, Y35P3 Adapter, Oil Stop: Yes, Tapered End: Yes, Die Index: 18 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): PAT750 Tool, U31RT Die, (4), Y35, Y39, Y46, Y750 Tool, U31RT Die With PUADP-1 Adapter, Conductor Type: Commercial Stranded Copper, Wire Strip Length: 1-3/5 IN



Product Details

General

Application	For Higher Voltage Applications From 5 KV Through 35 KV
Color Code	Red
Connector Type	Splice
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Electro Tin plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSP-T, High Voltage, Long Barrel
UPC	781810001325

Dimensions

Dimension - B Length inch	1.35 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.83 in
Dimension - Strip Length inch	1-3/5 in

Conductor Related

Conductor - Copper Str Size	350 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)