



YSR10CFX12CLTCKITC

by Burndy
Catalog ID: YSR10CFX12CLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel
A:#10AWG(Flex-Str) Barrel B:#12AWG(Flex-Str), Standard Barrel,
Electro-Tin Plated

Product Details

General

Connector Type	Reducer;Splice
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810473993
UPC 12 Digit	7818104739933

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - L Length Overall mm	37 mm
Dimension - Length BB inch	0.66 in
Dimension - Length Overall inch	1.45 in
Dimension - Strip Length inch	0.63 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size A Range	#14-#10 AWG
Conductor - Copper Flex G Size B Range	#14-#10 AWG
Conductor - Copper Flex H Size A Range	#14-#10 AWG
Conductor - Copper Flex H Size B Range	#14-#10 AWG
Conductor - Copper Flex I Size A Range	#14-#10 AWG
Conductor - Copper Flex I Size B Range	#14-#10 AWG
Conductor - Copper Flex K Size A Range	#14-#10 AWG

Conductor - Copper Flex K Size B Range	#14-#10 AWG
Conductor - Copper Flex M Size A Range	#14-#10 AWG
Conductor - Copper Flex M Size B Range	#14-#10 AWG
Conductor - Copper Solid Size A	12;11;10
Conductor - Copper Solid Size B	12;11;10
Conductor - Copper Str Size A Range	#14-#10 AWG
Conductor - Copper Str Size B	10 AWG
Conductor - Copper Str Size B Range	10 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)