



YSR25FX4CFXLTCKITC

by Burndy
Catalog ID: YSR25FX4CFXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel
A:1/0AWG(Flex-Str) Barrel B:#4AWG(Flex-Str), Standard Barrel, Electro-
Tin Plated

Product Details

General

Color Code - Side A	Pink
Color Code - Side B	Gray
Connector Type	Reducer;Splice
Die Index - Element A	12
Die Index - Element B	8
Die Index Run Side	12
Die Index Tap Side	8
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810429426
UPC 12 Digit	7818104294266

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.04 in
Dimension - L Length Overall mm	55 mm
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	2.27 in
Dimension - Strip Length inch	1.01 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size A	1/0 AWG
----------------------------------	---------

Conductor - Copper Flex G Size B	4 AWG
Conductor - Copper Flex H Size A	1/0 AWG
Conductor - Copper Flex H Size B	4 AWG
Conductor - Copper Flex I Size A	1/0 AWG
Conductor - Copper Flex I Size B	4 AWG
Conductor - Copper Flex K Size A	1/0 AWG
Conductor - Copper Flex K Size B	4 AWG
Conductor - Copper Flex M Size A	1/0 AWG
Conductor - Copper Flex M Size B	4 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	4 AWG
Conductor - Copper Str Size B Range	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)