



YSR282CFXLTCKITC

by Burndy
Catalog ID: YSR282CFXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:4/0
AWG(Str) Barrel B:#2 AWG(Flex-Str), Standard Barrel, Electro-Tin Plated

Product Details

General

Color Code - Side A	Purple
Color Code - Side B	Brown
Connector Type	Reducer;Splice
Die Index - Element A	15
Die Index - Element B	10
Die Index Run Side	15
Die Index Tap Side	10
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810345566
UPC 12 Digit	7818103455666

Dimensions

Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.30 in
Dimension - L Length Overall mm	69 mm
Dimension - Length BB inch	0.82 in
Dimension - Length Overall inch	2.70 in
Dimension - Strip Length inch	1.24 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size B	2 AWG
Conductor - Copper Flex H Size B	2 AWG

Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size A	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)