



## YSR2CFX6CFXLTCKITC

by Burndy  
Catalog ID: YSR2CFX6CFXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:2 AWG(Str)  
Barrel B:#6 AWG(Flex-Str), Standard Barrel, Electro-Tin Plated

### Product Details

#### General

Color Code - Side A	Brown
Color Code - Side B	Blue
Connector Type	Reducer;Splice
Die Index - Element A	10
Die Index - Element B	7
Die Index Run Side	10
Die Index Tap Side	7
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810345764
UPC 12 Digit	7818103457644

#### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - L Length Overall mm	50 mm
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	1.96 in
Dimension - Strip Length inch	0.78 in

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	6 AWG

Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex I Size A	2 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Flex M Size B	6 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)