



YSR3129FXTEL20

by Burndy
Catalog ID: YSR3129FXTEL20

Prop 65 Notice

Cu Compression Reducer/Splice Telecom Kit, Long Barrel, 350 kcmil Str. (Brrl A), 4/0 AWG Flex(Brrl B)

Product Details

General

Color Code - Side A	Red
Color Code - Side B	Yellow
Connector Type	Reducer;Splice
Die Index Run Side	18
Die Index Tap Side	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810345276
UPC 12 Digit	7818103452766

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.51 in
Dimension - L Length Overall mm	129 mm
Dimension - Length BB inch	2.36 in
Dimension - Length Overall inch	5.06 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size A	4/0 AWG
Conductor - Copper Flex G Size B	4/0 AWG
Conductor - Copper Flex H Size A	4/0 AWG
Conductor - Copper Flex H Size B	4/0 AWG
Conductor - Copper Flex I Size A	4/0 AWG

Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex K Size A	4/0 AWG
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size A	4/0 AWG

Certifications and Compliance

Certification - UL Listed Direct Burial	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)