



YSR3431LTCKITC

by Burndy
Catalog ID: YSR3431LTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:500
kcmil(Str) Barrel B: 350 KCMIL (Str), Standard Barrel, Electro-Tin Plated

Product Details

General

Color Code - Side A	Brown
Color Code - Side B	Red
Connector Type	Reducer;Splice
Die Index - Element A	20
Die Index - Element B	18
Die Index Run Side	20
Die Index Tap Side	18
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810344873
UPC 12 Digit	7818103448733

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - L Length Overall mm	93 mm
Dimension - Length BB inch	1.49 in
Dimension - Length Overall inch	3.66 in
Dimension - Strip Length inch	1.60 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex H Size B Range	N/A
--	-----

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)