



## YSR34FX28FXLTCKITC

by Burndy  
Catalog ID: YSR34FX28FXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:350 kcmil(Flex-Str) Barrel B:4/0 AWG(Flex-Str), Standard Barrel, Electro-Tin Plated

## Product Details

### General

Color Code - Side A	Blue
Color Code - Side B	Purple
Connector Type	Reducer;Splice
Die Index - Element A	19;L80
Die Index - Element B	15
Die Index Run Side	19;L80
Die Index Tap Side	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810345085
UPC 12 Digit	7818103450855

### Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - L Length Overall mm	98 mm
Dimension - Length BB inch	1.43 in
Dimension - Length Overall inch	3.86 in
Dimension - Strip Length inch	1.60 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size A Range	350 kcmil
Conductor - Copper Flex G Size B	4/0 AWG
Conductor - Copper Flex G Size B Range	4/0 AWG
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B	4/0 AWG
Conductor - Copper Flex H Size B Range	4/0 AWG
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size A Range	350 kcmil
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex I Size B Range	4/0 AWG
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size B Range	4/0 AWG
Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Flex M Size A Range	350 kcmil
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)