



YSR3929FXLTCKITC

by Burndy
Catalog ID: YSR3929FXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:750
kcmil(Str) Barrel B: 4/0 AWG(Flex-Str), Standard Barrel, Electro-Tin
Plated

Product Details

General

| | |
|------------------------|----------------------|
| Color Code - Side A | Black |
| Color Code - Side B | Yellow |
| Connector Type | Reducer;Splice |
| Die Index - Element A | 24 |
| Die Index - Element B | 16 |
| Die Index Run Side | 24 |
| Die Index Tap Side | 16 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYREDUCER™ |
| UPC | 781810472316 |
| UPC 12 Digit | 7818104723166 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 1-3/4 in |
| Dimension - B Length inch | 1.78 in |
| Dimension - L Length Overall mm | 117 mm |
| Dimension - Length BB inch | 1.44 in |
| Dimension - Length Overall inch | 4.59 in |
| Dimension - Strip Length inch | 1.67 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--|-----------|
| Conductor - Copper Flex I Size B | 4/0 AWG |
| Conductor - Copper Flex K Size B | 4/0 AWG |
| Conductor - Copper Flex K Size B Range | 4/0 AWG |
| Conductor - Copper Flex M Size B | 4/0 AWG |
| Conductor - Copper Flex M Size B Range | 4/0 AWG |
| Conductor - Copper Str Size | 750 kcmil |
| Conductor - Copper Str Size A | 750 kcmil |
| Conductor - Copper Str Size A Range | 750 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)