



# YSR44FX31LTCKITC

by Burndy  
Catalog ID: YSR44FX31LTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:750 kcmil(Flex-Str) Barrel B: 350 kcmil(Str), Standard Barrel, Electro-Tin Plated

## Product Details

### General

Color Code - Side A	Yellow
Color Code - Side B	Red
Connector Type	Reducer;Splice
Die Index - Element A	L115
Die Index - Element B	18
Die Index Run Side	L115
Die Index Tap Side	18
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810344354
UPC 12 Digit	7818103443544

### Dimensions

Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - L Length Overall mm	132 mm
Dimension - Length BB inch	1.49 in
Dimension - Length Overall inch	5.18 in
Dimension - Strip Length inch	1.96 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size A	750 kcmil
----------------------------------	-----------

Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size B Range	350 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)