



# YSR44FX34FXLTCKITC

by Burndy  
Catalog ID: YSR44FX34FXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A:750 kcmil(Flex-Str) Barrel B: 350 kcmil(Flex-Str), Standard Barrel, Electro-Tin Plated

## Product Details

### General

|                        |                      |
|------------------------|----------------------|
| Color Code - Side A    | Yellow               |
| Color Code - Side B    | Blue                 |
| Connector Type         | Reducer;Splice       |
| Die Index - Element A  | L115                 |
| Die Index - Element B  | 19;L80               |
| Die Index Run Side     | L115                 |
| Die Index Tap Side     | 19;L80               |
| Feature - Barrel Style | Skived               |
| Feature - Barrel Type  | Standard             |
| Material               | Copper               |
| Plated                 | Y                    |
| Plating Type           | Tin - Electro Plated |
| Temperature Rating     | 194                  |
| Trade Name             | HYREDUCER™           |
| UPC                    | 781810466216         |
| UPC 12 Digit           | 7818104662166        |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - B Length fraction   | 2-1/16 in |
| Dimension - B Length inch       | 2.09 in   |
| Dimension - L Length Overall mm | 125 mm    |
| Dimension - Length BB inch      | 1.69 in   |
| Dimension - Length Overall inch | 4.91 in   |
| Dimension - Strip Length inch   | 1.96 in   |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

### Conductor Related

|                                  |           |
|----------------------------------|-----------|
| Conductor - Copper Flex G Size A | 750 kcmil |
|----------------------------------|-----------|

|  |           |
|--|-----------|
| Conductor - Copper Flex G Size A Range | 750 kcmil |
| Conductor - Copper Flex G Size B       | 350 kcmil |
| Conductor - Copper Flex G Size B Range | 350 kcmil |
| Conductor - Copper Flex H Size A       | 750 kcmil |
| Conductor - Copper Flex H Size A Range | 750 kcmil |
| Conductor - Copper Flex H Size B       | 350 kcmil |
| Conductor - Copper Flex H Size B Range | 350 kcmil |
| Conductor - Copper Flex I Size A       | 750 KCMIL |
| Conductor - Copper Flex I Size A Range | 750 KCMIL |
| Conductor - Copper Flex I Size B       | 350 kcmil |
| Conductor - Copper Flex I Size B Range | 350 kcmil |
| Conductor - Copper Flex K Size A       | 750 KCMIL |
| Conductor - Copper Flex K Size A Range | 750 KCMIL |
| Conductor - Copper Flex K Size B       | 350 kcmil |
| Conductor - Copper Flex K Size B Range | 350 kcmil |
| Conductor - Copper Flex M Size A       | 750 KCMIL |
| Conductor - Copper Flex M Size A Range | 750 KCMIL |
| Conductor - Copper Flex M Size B       | 350 kcmil |
| Conductor - Copper Flex M Size B Range | 350 kcmil |
| Conductor - Copper Str Size A          | 750 kcmil |
| Conductor - Copper Str Size A Range    | 750 kcmil |
| Conductor - Copper Str Size B          | 350 kcmil |
| Conductor - Copper Str Size B Range    | 350 kcmil |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)