



YSR4CFX6CFXLTCKITC

by Burndy
Catalog ID: YSR4CFX6CFXLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A: #4 AWG (Flex-Str) Barrel B: #6 AWG (Flex-Str), Standard Barrel, Electro-Tin Plated

Product Details

General

Color Code - Side A	Gray
Color Code - Side B	Blue
Connector Type	Reducer;Splice
Die Index - Element A	8
Die Index - Element B	7
Die Index Run Side	8
Die Index Tap Side	7
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810345801
UPC 12 Digit	7818103458011

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.74 in
Dimension - L Length Overall mm	42 mm
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	1.67 in
Dimension - Strip Length inch	0.71 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size A	4 AWG
Conductor - Copper Flex G Size A Range	4 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Flex G Size B Range	6 AWG
Conductor - Copper Flex H Size A	4 AWG
Conductor - Copper Flex H Size A Range	4 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex H Size B Range	6 AWG
Conductor - Copper Flex I Size A	4 AWG
Conductor - Copper Flex I Size A Range	4 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex I Size B Range	6 AWG
Conductor - Copper Flex K Size A	4 AWG
Conductor - Copper Flex K Size A Range	4 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex K Size B Range	6 AWG
Conductor - Copper Flex M Size A	4 AWG
Conductor - Copper Flex M Size A Range	4 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Size B Range	6 AWG
Conductor - Copper Str Size B	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)