



# YSR8CFX10CLTCKITC

by Burndy  
Catalog ID: YSR8CFX10CLTCKITC

Prop 65 Notice

Compression CU Reducer/Splice kit, W/InspWindow, Barrel A: #8 AWG (Flex-Str) Barrel B: #10 AWG (Str), Standard Barrel, Electro-Tin Plated

## Product Details

### General

Color Code - Side A	Red
Connector Type	Reducer;Splice
Die Index - Element A	49
Die Index Run Side	49
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810473979
UPC 12 Digit	7818104739799

### Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.57 in
Dimension - L Length Overall mm	36 mm
Dimension - Length BB inch	0.66 in
Dimension - Length Overall inch	1.41 in
Dimension - Strip Length inch	0.57 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size A	8 AWG
Conductor - Copper Flex G Size A Range	8 AWG
Conductor - Copper Flex G Size B	10 AWG
Conductor - Copper Flex G Size B Range	10 AWG

Conductor - Copper Flex H Size A	8 AWG
Conductor - Copper Flex H Size A Range	8 AWG
Conductor - Copper Flex H Size B	10 AWG
Conductor - Copper Flex H Size B Range	10 AWG
Conductor - Copper Flex I Size A	8 AWG
Conductor - Copper Flex I Size A Range	8 AWG
Conductor - Copper Flex I Size B	10 AWG
Conductor - Copper Flex I Size B Range	10 AWG
Conductor - Copper Flex K Size A	8 AWG
Conductor - Copper Flex K Size A Range	8 AWG
Conductor - Copper Flex K Size B	10 AWG
Conductor - Copper Flex K Size B Range	10 AWG
Conductor - Copper Flex M Size A	8 AWG
Conductor - Copper Flex M Size A Range	8 AWG
Conductor - Copper Flex M Size B	10 AWG
Conductor - Copper Flex M Size B Range	10 AWG
Conductor - Copper Solid Size A	6
Conductor - Copper Solid Size B	12;11;10
Conductor - Copper Str Size B	10 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)